

测温环外径与温度对照表

| 产品型号(Type): ETC 012 | | | | 规格 (Dimensions): $\Phi_o 20 \times \Phi_i 10 \times h 7\text{mm}$, 兰色 (Blue) | | | | | |
|---|--------|-------------|--------|---|--------|-------------|--------|-------------|--------|
| 适用温度范围(Temperature): 1450 °C ~ 1750 °C | | | | 试验条件(Condition): 空气气氛下保温 1 小时 | | | | | |
| Φ (mm) | T (°C) | Φ (mm) | T (°C) | Φ (mm) | T (°C) | Φ (mm) | T (°C) | Φ (mm) | T (°C) |
| 19.41 | 1450 | 18.96 | 1539 | 18.51 | 1601 | 18.06 | 1651 | 17.61 | 1697 |
| 19.40 | 1451 | 18.95 | 1540 | 18.50 | 1602 | 18.05 | 1652 | 17.60 | 1698 |
| 19.39 | 1453 | 18.94 | 1541 | 18.49 | 1603 | 18.04 | 1653 | 17.59 | 1700 |
| 19.38 | 1455 | 18.93 | 1543 | 18.48 | 1605 | 18.03 | 1654 | 17.58 | 1701 |
| 19.37 | 1457 | 18.92 | 1544 | 18.47 | 1606 | 18.02 | 1655 | 17.57 | 1702 |
| 19.36 | 1459 | 18.91 | 1546 | 18.46 | 1607 | 18.01 | 1656 | 17.56 | 1704 |
| 19.35 | 1461 | 18.90 | 1548 | 18.45 | 1608 | 18.00 | 1657 | 17.55 | 1705 |
| 19.34 | 1464 | 18.89 | 1549 | 18.44 | 1610 | 17.99 | 1658 | 17.54 | 1706 |
| 19.33 | 1466 | 18.88 | 1550 | 18.43 | 1611 | 17.98 | 1659 | 17.53 | 1708 |
| 19.32 | 1468 | 18.87 | 1551 | 18.42 | 1612 | 17.97 | 1660 | 17.52 | 1709 |
| 19.31 | 1471 | 18.86 | 1553 | 18.41 | 1613 | 17.96 | 1661 | 17.51 | 1711 |
| 19.30 | 1474 | 18.85 | 1554 | 18.40 | 1614 | 17.95 | 1662 | 17.50 | 1712 |
| 19.29 | 1477 | 18.84 | 1555 | 18.39 | 1616 | 17.94 | 1663 | 17.49 | 1714 |
| 19.28 | 1479 | 18.83 | 1557 | 18.38 | 1617 | 17.93 | 1663 | 17.48 | 1715 |
| 19.27 | 1482 | 18.82 | 1558 | 18.37 | 1618 | 17.92 | 1664 | 17.47 | 1717 |
| 19.26 | 1485 | 18.81 | 1560 | 18.36 | 1619 | 17.91 | 1665 | 17.46 | 1718 |
| 19.25 | 1488 | 18.80 | 1561 | 18.35 | 1620 | 17.90 | 1666 | 17.45 | 1720 |
| 19.24 | 1490 | 18.79 | 1562 | 18.34 | 1621 | 17.89 | 1667 | 17.44 | 1722 |
| 19.23 | 1492 | 18.78 | 1564 | 18.33 | 1623 | 17.88 | 1668 | 17.43 | 1723 |
| 19.22 | 1495 | 18.77 | 1565 | 18.32 | 1624 | 17.87 | 1669 | 17.42 | 1725 |
| 19.21 | 1497 | 18.76 | 1567 | 18.31 | 1625 | 17.86 | 1670 | 17.41 | 1726 |
| 19.20 | 1499 | 18.75 | 1568 | 18.30 | 1626 | 17.85 | 1671 | 17.40 | 1728 |
| 19.19 | 1502 | 18.74 | 1569 | 18.29 | 1627 | 17.84 | 1672 | 17.39 | 1729 |
| 19.18 | 1504 | 18.73 | 1571 | 18.28 | 1628 | 17.83 | 1673 | 17.38 | 1731 |
| 19.17 | 1506 | 18.72 | 1572 | 18.27 | 1629 | 17.82 | 1674 | 17.37 | 1732 |
| 19.16 | 1507 | 18.71 | 1574 | 18.26 | 1630 | 17.81 | 1675 | 17.36 | 1733 |
| 19.15 | 1509 | 18.70 | 1575 | 18.25 | 1631 | 17.80 | 1676 | 17.35 | 1735 |
| 19.14 | 1511 | 18.69 | 1576 | 18.24 | 1633 | 17.79 | 1677 | 17.34 | 1736 |
| 19.13 | 1513 | 18.68 | 1578 | 18.23 | 1634 | 17.78 | 1678 | 17.33 | 1738 |
| 19.12 | 1514 | 18.67 | 1579 | 18.22 | 1635 | 17.77 | 1679 | 17.32 | 1739 |
| 19.11 | 1516 | 18.66 | 1581 | 18.21 | 1636 | 17.76 | 1680 | 17.31 | 1740 |
| 19.10 | 1518 | 18.65 | 1582 | 18.20 | 1637 | 17.75 | 1681 | 17.30 | 1742 |
| 19.09 | 1520 | 18.64 | 1583 | 18.19 | 1638 | 17.74 | 1683 | 17.29 | 1743 |
| 19.08 | 1521 | 18.63 | 1585 | 18.18 | 1639 | 17.73 | 1684 | 17.28 | 1744 |
| 19.07 | 1523 | 18.62 | 1586 | 18.17 | 1640 | 17.72 | 1685 | 17.27 | 1745 |
| 19.06 | 1524 | 18.61 | 1587 | 18.16 | 1641 | 17.71 | 1686 | 17.26 | 1746 |
| 19.05 | 1526 | 18.60 | 1589 | 18.15 | 1642 | 17.70 | 1687 | 17.25 | 1747 |
| 19.04 | 1527 | 18.59 | 1590 | 18.14 | 1643 | 17.69 | 1688 | 17.24 | 1748 |
| 19.03 | 1529 | 18.58 | 1592 | 18.13 | 1644 | 17.68 | 1689 | 17.23 | 1749 |
| 19.02 | 1530 | 18.57 | 1593 | 18.12 | 1645 | 17.67 | 1690 | 17.22 | 1750 |
| 19.01 | 1532 | 18.56 | 1594 | 18.11 | 1646 | 17.66 | 1691 | | |
| 19.00 | 1533 | 18.55 | 1596 | 18.10 | 1647 | 17.65 | 1692 | | |
| 18.99 | 1534 | 18.54 | 1597 | 18.09 | 1648 | 17.64 | 1693 | | |
| 18.98 | 1536 | 18.53 | 1598 | 18.08 | 1649 | 17.63 | 1694 | | |
| 18.97 | 1537 | 18.52 | 1600 | 18.07 | 1650 | 17.62 | 1696 | | |

检验工程师 (Inspector): 黄满连

生产日期 (Date): 2020 - 08-30